




## How do I fit “slanted with overhang” grain carts?

Drawing at right shows a grain cart with an uneven angle across the box top. Galvanized caps will NOT fit this box; fabric caps must be ordered instead. For proper fit, a box detail sheet must be filled out with each of the measurements noted below.





When you fill out the required box detail sheet for grain carts and wagons, you will see illustrated cart styles for “slanted with overhang” and “slanted with angle and overhang” configurations. These require fabric caps as well as special brackets on the sloped side of the cart.

Our **Adjustable Bow Bracket** bolts to the sloped side of the cart and adjusts to the angle of the extension slope. You’ll need one for each bow on the sloped side of the cart, including the bows for the fabric caps.

Place bow brackets vertically to create a distance of three to six inches between the bend in the bow shank and where the tarp comes in contact with the bow to reduce tarp wear. When marking bows, cut to the exact length. If the bow is cut short and not welded to the bow shank, pressure from the tarp will flatten the arch.

For additional information about Shur-Co® products, give us a call at **1.800.474.8756** Monday through Friday, from 8:00 a.m. to 5:00 p.m. Central Time. Our friendly and knowledgeable Customer Service Representatives will be happy to answer your questions. Or log on to our website at [www.shurco.com](http://www.shurco.com).



Above: Position single bow brackets according to the width of the rails, with short side up for lip in boxes and tall side up for lip out boxes. If using the Adjustable Bow Bracket for carts with sloped side rails, position the short side down.